



RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25

- 技术要求：
- 打铜底0.5-1μm, 镍2-2.5μm, 哑锡3-5μm。
 - 不得有变形, 毛刺等现象。
 - 插脚尖部符合可焊性要求。
 - 螺纹需符合通止规/止针要求。
 - 螺纹扭矩：1.0Nm。
 - 额定扭矩：60A。
 - X为重点测量尺寸。



>30 ±0.40	x.°±	PART NO: TR44105130-1480	XFCN 兴飞连接器			
6-30 ±0.30	.x°±					
0-6 ±0.20	.xx°±					
ANGLES ±1°	.xxx°±					
UNITS:	mm					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		TITLE: PCB SOLDERING TERMINAL		0769-82001899		
				www.xfconn.com		
				DWG NO: /		
				APPD		
		CHKD		VIEW		
		DRAW	Wang	SCALE	SHEET	REV
		DATE	2023.11.25	NONE	1:1	A1

1	插脚		H62(Y2)	1
序号	名称	零件编号	材质	数量