




RoHS

| REV | ECN NO. | DESRPTION | DESIGN | APPROVAL | DATE       |
|-----|---------|-----------|--------|----------|------------|
| A1  | NEW     | 更换图框      |        |          | 2023.11.25 |

- 技术要求:
- 打铜底0.5-1μm, 镍2-2.5μm, 哑锡3-5μm。
  - 垫片铆好后不得有松动现象。
  - 插脚尖部符合可焊性要求。
  - 螺纹需符合通止规/止针要求。
  - 螺纹扭矩: 1.0Nm.
  - 额定扭矩: 50A.
  - X为重点测量尺寸。



|                                                                                                                                                                          |                   |                                         |                                 |                                                                                                                  |                  |                |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|-----------------------------------------|---------------------------------|------------------------------------------------------------------------------------------------------------------|------------------|----------------|
| <div>&gt;30 ±0.40</div>                                                                                                                                                  | <div>x.°±</div>   | <div>PART NO:<br/>TT34086077-0910</div> | <div>XFCN兴飞连接器</div>            |                                                                                                                  |                  |                |
| <div>6-30 ±0.30</div>                                                                                                                                                    | <div>.x°±</div>   |                                         |                                 |                                                                                                                  |                  |                |
| <div>0-6 ±0.20</div>                                                                                                                                                     | <div>.xx°±</div>  |                                         | <div>0769-82001899</div>        |                                                                                                                  |                  |                |
| <div>ANGLES ±1°</div>                                                                                                                                                    | <div>.xxx°±</div> |                                         | <div>www.xfconn.com</div>       |                                                                                                                  |                  |                |
| <div>UNITS:</div>                                                                                                                                                        | <div>mm</div>     |                                         | <div>DWG NO:</div> <div>/</div> |                                                                                                                  |                  |                |
| <div>THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN</div> |                   | <div>APPD</div>                         |                                 | <div>VIEW</div> <div></div> |                  |                |
|                                                                                                                                                                          |                   | <div>CHKD</div>                         |                                 |                                                                                                                  |                  |                |
|                                                                                                                                                                          |                   | <div>DRAW</div>                         | <div>Wang</div>                 | <div>SCALE</div>                                                                                                 | <div>SHEET</div> | <div>REV</div> |
|                                                                                                                                                                          |                   | <div>DATE</div>                         | <div>2023.11.27</div>           | <div>NONE</div>                                                                                                  | <div>1:1</div>   | <div>A1</div>  |

|    |     |      |        |    |
|----|-----|------|--------|----|
| 2  | 垫 片 |      | SPCC   | 1  |
| 1  | 插 脚 |      | T2(Y2) | 1  |
| 序号 | 名 称 | 零件编号 | 材 质    | 数量 |