




A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 20A 发热电流: Ui: AC250V, Ith: 20A						12. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	2. Rated current:16A/AC110V/220V 16A/DC12V/24V 额定电流:16A/AC110V/220V 16A/DC12V/24V						13. Compression torque: ≤ 4N 按压扭力: ≤4N						
	3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min						14. Electrical life: 30000 cycles 电气寿命: 30000 cycles						
2	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						15. mechanical: 200000cycles 机械寿命: 200000cycles						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						16. Operation method:Self-locking 操作方式: 自锁式						
	6. Pressing stroke:3.50mm ± 0.10 按压行程:3.50mm ± 0.10						17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	7. Contact stroke:1.35mm±0.10 接触行程 :1.35mm±0.10						18. LED lamp lifespan: 40000h LED寿命: 40000h						
3	8. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration						19. LED color: Red LED颜色: 红色						
	9. Nut assembly torque:5-14N 螺帽装配力矩:5-14N						20. LED Lamp Voltage: 24V LED灯电压: 24V						
	10. Protection level:IP67 防护等级:IP67						21. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	11. Explosion prevention level: IK10 防暴等级: IK10												
4	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 Switch function wire: blue wire NO (1²mm) 开关功能线材: 蓝线NO (1²mm)												
5	2.2 LED functional wires: red positive wire, black negative wire (0.5²mm) LED功能线材: 红线正极、黑线负极												
	2.3 LED light with five pole beads, can be lit without the need to separate positive and negative poles LED灯五极灯珠, 无需分正负极也可点亮												
	A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992502P124RS	
A2				DATE				2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1				ROCPCU TECHNOLOGY CO.,LTD									
REV	DATE	REVISION	DESCRIPTION							ISSUE	ANGULAR		
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													
A		B		C		D		E		F		G	

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission

		A			B			C			D			E			F			G		
材质参数																						
1		10	Bush 衬套			PBT			1													
		9	LEDpin LED引脚			Brass 黄铜			1			Silvering 镀银										
		8	Base 底座			PBT			1													
		7	Pin 引脚			Brass 黄铜			1			Silvering 镀银										
2		6	Contact material 接触材质			silver alloy 银合金			1													
		5	luminous zone 发光区			PC 塑胶			1													
		4	Arm nut 固定螺帽			Brass 黄铜			1			nickeling 镀镍										
		3	Oring O型圈			Silica gel 硅胶			1													
3		2	Housing 外壳			SUS 不锈钢			1													
		1	Key 按键			SUS 不锈钢			1													
		NO 序号	Part name 部件名			Material 材料			QTY 数量			Remark 备注										
4		A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:									
		A3						DRAWN BY FUYUAN		CHECKED BY	COCO	MODEL NO: TP992502P124RS										
		A2						DATE 2019		APPROVAL B	ALEN	Https: www.rocpcu.tw										
		A1						X.XX ± 0.10		ROCPCU TECHNOLOGY CO.,LTD												
REV	DATE	REVISION	DESCRIPTION	ISSUE	X.X ± 0.15																	
							X ± 0.25															
							ANGULAR															
														Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission								
		A			B			C			D			E			F			G		