



	A	B	C	D	E	F	G																																																														
1	性能参数						1																																																														
2	1. Nut assembly torque: 5-14N 螺帽装配力矩: 5-14N 2. Protection level: IP67 防护等级: IP67 3. Explosion prevention level: IK10 防爆等级: IK10 4. Working environment temperature: -20 °C ~ +55 °C 工作环境温度: -20 °C ~ +55 °C 5. LED voltage: 6V LED 电压: 6V 6. LED lamp power consumption: 20mA以下 LED灯功耗: 20mA以下 7. LED lamp lifespan: 40000h LED寿命: 40000h 8. LED color: Red LED颜色: 红色						2																																																														
3							3																																																														
4	连接形式						4																																																														
5	1. Welding temperature of wire: 320 ± 20 °C 线材焊接温度: 320±20°C Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下 2. Can be used with dedicated connectors: 可配专用接插件使用: 2.1 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极					5																																																															
<table border="1"> <tr> <td>A4</td> <td></td> <td></td> <td></td> <td rowspan="6">  <b>台普</b>  <b>ROCPU</b> </td> <td rowspan="2">COMMON TOLERANCE</td> <td>UNIT</td> <td>MM</td> <td>PROJECTED</td> <td></td> <td>PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td></td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td>MODEL NO:TP91950P6RS</td> </tr> <tr> <td>A2</td> <td></td> <td></td> <td>X.XX</td> <td>± 0.10</td> <td rowspan="4">DATE</td> <td>2019</td> <td>APPROVAL</td> <td>B</td> <td>ALEN</td> <td>Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a></td> </tr> <tr> <td>A1</td> <td></td> <td></td> <td>X.X</td> <td>± 0.15</td> <td>2019</td> <td>APPROVAL</td> <td>B</td> <td>ALEN</td> <td>Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a></td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION DESCRIPTION</td> <td>ISSUE</td> <td>X</td> <td>± 0.25</td> <td>2019</td> <td>APPROVAL</td> <td>B</td> <td>ALEN</td> <td>Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td>ANGULAR</td> <td>—</td> <td>2019</td> <td>APPROVAL</td> <td>B</td> <td>ALEN</td> <td>Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a></td> </tr> </table>	A4				 <b>台普</b> <b>ROCPU</b>	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:	A3			DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP91950P6RS	A2			X.XX	± 0.10	DATE	2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>	A1			X.X	± 0.15	2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>	REV	DATE	REVISION DESCRIPTION	ISSUE	X	± 0.25	2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>					ANGULAR	—	2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>	<b>ROCPU TECHNOLOGY CO., LTD</b> <small>Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission</small>						
A4				 <b>台普</b> <b>ROCPU</b>			COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:																																																									
A3			DRAWN BY			FUYUAN		CHECKED BY	COCO	MODEL NO:TP91950P6RS																																																											
A2			X.XX			± 0.10	DATE	2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>																																																									
A1			X.X			± 0.15		2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>																																																									
REV	DATE	REVISION DESCRIPTION	ISSUE			X		± 0.25	2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>																																																								
					ANGULAR	—		2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>																																																									
	A	B	C	D	E	F	G																																																														

	A	B	C	D	E	F	G					
材质参数												
1	10											
2	9											
3	8											
4	7	luminous zone 发光区		PC 塑料	1							
5	6	LEDpin LED脚		Brass 黄铜	1	Silvering 镀银						
6	5	LED Base LED基座		PC 塑料	1							
7	4	Arm nut 固定螺帽		Brass 黄铜	1	nickeling 镀镍						
8	3	Oring O型圈		Silica gel 硅胶	1							
9	2	Housing 外壳		SUS 不锈钢	1							
10	1	Base 底座		PA46	1	Silvering 镀银						
	NO 序号	Part name 部件名		Material 材料	QTY 数量	Remark 备注						
5	A4			 <b>台普</b> <b>ROCPU</b>	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:		
A3			X.XX		± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91950P6RS		
A2			X.X		± 0.15	DATE	2019	APPROVAL	B	ALEN	Https: <a href="http://www.rocpu.tw">www.rocpu.tw</a>	
A1			X		± 0.25	<b>ROCPU TECHNOLOGY CO., LTD</b>						
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
		A	B			C	D	E	F	G		