











A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:				
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92229P224RS				
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD								
					X	± 0.25									
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission								
	A			B			C		D		E		F		G

A		B		C		D		E		F		G	
1	性能参数												
	1. Rated current:0.1A/DC36V 额定电流:0.1A/DC36V						13. Electrical life: 200000 cycles 电气寿命: 200000 cycles						
	2. Insulation resistance:≥50MΩ 绝缘电阻 :≥50MΩ						14. mechanical: 1000000cycles 机械寿命: 1000000cycles						
	3. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						15. Operation method:Unlocking 操作方式: 无锁式						
	4. Pressing stroke:0.50mm ± 0.10 按压行程:0.50mm ± 0.10						16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	5. Contact stroke:0.50mm±0.10 接触行程 :0.50mm±0.10						17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	6. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃						18. LED lamp lifespan: 40000h LED寿命: 40000h						
	7. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration						19. LED color: Red LED颜色: 红色						
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
	9. Protection level:IP67 防护等级:IP67												
2													
	10. Explosion prevention level: IK08 防暴等级: IK08												
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃												
	12. Compression torque: ≤ 3N 按压扭力: ≤3N												
3													
4													
5													

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92229P224RS		
A2						DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission						
A		B		C		D		E		F		G	

A		B		C		D		E		F		G																																																									
材质参数																																																																					
8		LEDpin LED脚		Brass 黄铜		1		Silvering 镀银																																																													
7		luminous zone 发光区		PC 塑料		1																																																															
6		Pin 引脚		Brass 黄铜		1		gold-plating 镀金																																																													
5		Base 基座		PBT		1																																																															
4		Arm nut 固定螺帽		Brass 黄铜		1		nickeling 镀镍																																																													
3		Oring O型圈		Silica gel 硅胶		1																																																															
2		Housing 外壳		SUS 不锈钢		1																																																															
1		Key 按键		SUS 不锈钢		1																																																															
NO 序号		Part name 部件名		Material 材料		QTY 数量		Remark 备注																																																													
<table border="1"> <tr> <td>A4</td> <td></td> <td></td> <td></td> <td rowspan="5">  台普 ROCPCU </td> <td colspan="2">COMMON TOLERANCE</td> <td>UNIT</td> <td>MM</td> <td>PROJECTED</td> <td></td> <td colspan="2">PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td></td> <td></td> <td>X.XX</td> <td>± 0.10</td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td colspan="2">MODEL NO: TP92229P224RS</td> </tr> <tr> <td>A2</td> <td></td> <td></td> <td></td> <td>X.X</td> <td>± 0.15</td> <td>DATE</td> <td>2019</td> <td>APPROVAL B</td> <td>ALEN</td> <td colspan="2">Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td> <td></td> <td></td> <td></td> <td>X</td> <td>± 0.25</td> <td colspan="6" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION</td> <td>DESCRIPTION</td> <td>ISSUE</td> <td>ANGULAR</td> <td></td> </tr> </table>														A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		A3				X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92229P224RS		A2				X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		A1				X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD						REV	DATE	REVISION	DESCRIPTION	ISSUE	ANGULAR	
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																										
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92229P224RS																																																										
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																										
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD																																																														
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR																																																															
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																																					