




	A	B	C	D	E	F	G					
1	性能参数				13. Electrical life: 100000 cycles 电气寿命: 100000 cycles							
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A				14. mechanical: 500000cycles 机械寿命: 500000cycles							
	2. Rated current:3A/DC36V 额定电流:3A/DC36V				15. Operation method:Self locking 操作方式: 自锁式							
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min				16. Power-frequency withstand voltage: 2000V/1min 工频耐压: 2000V/1min							
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ				17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下							
2	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ				18. LED lamp lifespan: 40000h LED寿命: 40000h							
	6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10				19. LED color: Yellow LED颜色: 黄色							
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10				20. LED Lamp Voltage: 24V LED灯电压: 24V							
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N				21. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N							
	9. Protection level:IP67 防护等级:IP67											
	10. Explosion prevention level: IK10 防暴等级: IK10											
3	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃											
	12. Compression torque: ≤ 3.5N 按压扭力: ≤3.5N											
	连接形式											
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下											
	2. Can be used with dedicated connectors: 可配专用接插件使用:											
4	2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿色(C) 蓝线(NO) 黄线(NC)											
	2.2 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极											
5	A4				COMMON TOLERANCE			UNIT	MM	PROJECTED		PRODUCT NAME:
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92235P224YS
	A2				X.XX ± 0.10			DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X.X ± 0.15			ROCPCU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION	DESCRIPTION	ISSUE	X ± 0.25						
						ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
	A		B		C		D	E	F		G	

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G																																																															
1	材质参数 <table border="1"> <tr> <td>10</td><td>luminous zone 发光区</td><td>PC 塑胶</td><td>1</td><td></td></tr> <tr> <td>9</td><td>LEDpin LED引脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>8</td><td>Base 底座</td><td>PA66</td><td>1</td><td></td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>gold-plating 镀金</td></tr> <tr> <td>6</td><td>Contact material 接触材质</td><td>silver alloy 银合金</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>5</td><td>LED Base LED基座</td><td>PA66</td><td>1</td><td></td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>1</td><td>Key 按键</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>						10	luminous zone 发光区	PC 塑胶	1		9	LEDpin LED引脚	Brass 黄铜	1	Silvering 镀银	8	Base 底座	PA66	1		7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金	6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银	5	LED Base LED基座	PA66	1		4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	SUS 不锈钢	1		1	Key 按键	SUS 不锈钢	1		NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1								
10	luminous zone 发光区	PC 塑胶	1																																																																			
9	LEDpin LED引脚	Brass 黄铜	1	Silvering 镀银																																																																		
8	Base 底座	PA66	1																																																																			
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金																																																																		
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银																																																																		
5	LED Base LED基座	PA66	1																																																																			
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																																		
3	Oring O型圈	Silica gel 硅胶	1																																																																			
2	Housing 外壳	SUS 不锈钢	1																																																																			
1	Key 按键	SUS 不锈钢	1																																																																			
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																																		
2							2																																																															
3							3																																																															
4							4																																																															
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td><td colspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr> <tr> <td>A3</td><td></td><td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td colspan="3">MODEL NO: TP92235P224YS</td></tr> <tr> <td>A2</td><td></td><td></td><td></td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td colspan="3">Https: www.rocpcu.tw</td></tr> <tr> <td>A1</td><td></td><td></td><td></td><td colspan="7" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td></tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td><td>ANGULAR</td><td>—</td><td colspan="6">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr> </table>						A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92235P224YS			A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			A1				ROCPCU TECHNOLOGY CO.,LTD							REV	DATE	REVISION	DESCRIPTION	ISSUE						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission						5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED			PRODUCT NAME:																																																										
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92235P224YS																																																													
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																													
A1					ROCPCU TECHNOLOGY CO.,LTD																																																																	
REV	DATE	REVISION	DESCRIPTION									ISSUE																																																										
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																															
	A	B	C	D	E	F	G																																																															