

东莞市博众电气有限公司


Dongguan Bozhong Electrical Co., Ltd

产品名称Product: FFC排线 B面（反面）

产品型号Part No: BTC10B-NP-TL-3-4

规格书

UL STYLE NO. 20624, Non Deca (43 μ m) Film , LFCu, Supporting Tape:0.225mm



P	T. L	W	SP	M	T	Ti	S1	S2	S3	S4	B	NO. OF CONDUCTOR
1. 00	25. 0	3. 50	2. 50	0. 50	0. 35	0. 130	3. 0	3. 0	4. 0	4. 0	0. 5	6
±0. 1	±2. 0	±0. 1	±0. 1	±0. 1	±0. 0 5	±0. 05	±1. 0	±1. 0	±1. 0	±1. 0	小于	
导体规格		扁平铜板					厚度 (CT)			0. 05		±0. 005
		镀锡皮厚度：1. 0 μ 以上					宽度 (CW)			0. 65		±0. 03

BTC10B-NP-XL-3-4

连接器 间距 导体数 绝缘体长度 接触片类型 导体长度 补强板长度 导体厚度 导体宽度



[illegible]

MATERIAL SPECIFICATION



PRODUCT		FLEXIBLE FLAT CABLE					
UL STYLE NO.		VOLTAGE RATING	OPERATING TEMPERATURE	UL FILE NO.	MARKING		
☐	AWM 2896	30V	80℃		AWM 2896 80℃ VW-1		
☒	AWM 20624	60V	80℃		AWM 20624 80℃ VW-1		
☐	AWM 20706	60V	105℃		AWM 20706 105℃ VW-1		
CONDUCTOR	SIZE (Gt×Gw)		RATED CURRENT	RESISTANCE	REMARKS		
	☐	0.1X1.27	2A	0.17Ω/M	* TIN PLATED COPPER WIRE		
	☐	0.1X0.8	2A	0.27Ω/M	:99.994% PURE COPPER		
	☐	0.1X0.7	2A	0.33Ω/M	* TOLERANCE OF THICKNESS		
	☐	0.1X0.65	2A	0.35Ω/M	:±0.005		
	☐	0.1X0.5	1A	0.42Ω/M	* TOLERANCE OF WIDTH		
	☐	0.1X0.3	1A	0.70Ω/M	:±0.03		
	☐	0.05X0.8	1A	0.53Ω/M	* EXTENSION RATE		
	☐	0.05X0.65	1A	0.63Ω/M	:OVER THAN 15%		
	☐	0.05X0.6	1A	0.65Ω/M	* STRAIN STRENGTH		
	☐	0.035X0.8	1A	0.83Ω/M	:OVER THAN 13Kgf/mm ²		
	☐	0.035X0.7	1A	0.60Ω/M	* PLATING THICKNESS		
	☐	0.035X0.6	1A	0.96Ω/M	:0.075 μ 以上		
	☐	0.035X0.3	0.5A	1.80Ω/M			
	☒	0.035X0.3	0.5	1.89Ω/M			
	☐	0.022X0.3	0.5A	3.18Ω/M			
	☐	0.1X0.5 (P)	0.5A	2.80Ω/M	* TIN PLATED PHOSPHORUS BRONZE WIRE		
LEAD FREE ☒				GOLD ☐			
INSULATION FILM	NO.	BASE FILM	ADHESIVE	TOTAL THICKNESS	REMARK	COLOR	
	☐	1	PET 25μm	35μm	60μm	REGULAR	☐ WHITE ☐ BLACK
	☒	2	PET 19μm	24μm	43μm	SUPER FLEX	☒ WHITE
	☒	3	PET 12μm	25μm	37μm	ULTRA FLEX	☐ WHITE
DECA FREE ☐							
SUPPORTING TAPE	NO.	BASE FILM	ADHESIVE	TOTAL THICKNESS	COLOR		
	☐	1	PET 125μm	35μm	160μm	☐ WHITE ☐ BLUE	
	☒	2	PET 190μm	35μm	225μm	☐ WHITE ☒ BLUE	
	☐	3	PET 215μm	35μm	250μm	☐ WHITE ☐ BLUE	
☐	4	PET 250μm	35μm	285μm	☐ WHITE ☐ BLUE		
EMI SHIELD	ALUMINIUM FOIL [μm] COPPER FOIL [μm] FABRIC TAPE [μm] LAMINATION [μm]						
DOUBLE SIDE TAPE							
DIELECTRIC VOLTAGE WITHSTAND TEST				AC 500V/10mA 1分钟			
INSULATION RESISTANCE TEST				DC 500V/100Ω/M			
AGING				85℃/96 HR			
FLEXIBILITY	GENERAL	10,000 Min (R5×240/Min×40mm/Reciprocating)					
	FLEX	100,000 Min (R5×240/Min×40mm/Reciprocating)					
	SUPER	3,000,000 Min (R5×240/Min×40mm/Reciprocating)					
	ULTRA	6,000,000 Min (R5×240/Min×40mm/Reciprocating)					
FLAMMABILITY		PASS UL VW-1					

Matters that demand special attention :

- * When insert to connector, please insert straight correctly with Joiner's supporting-tape.



- * When insert to connector, please avoid excessive force.



- * After insert to connector, shall be not bend at supporting-tape excessive because Joiner is broken

