







CATEGORY	DESCRIPTION	P/N #
CONNECTOR	3288 金针 90度插板 (弯脚)	MJ3288-XX11-HR1

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2016.10.12
A02	—	增加颜色选项	YST	2019.11.21



MJ3288-XX11-HR1	
TABLE1	TABLE2
X HOUSING	X Terminal Plating
B BLACK	0 G/F Plating
Y YELLOW	1 Au 3u" Plating
	2 Au 6u" Plating
	3 Au 15u" Plating
	4 Au 30u" Plating

- 1.RJ ELECTRICAL CHARACTERISTICS
- 1-1: VOLTAGE:125V AC RMS
 - 1-2: CURRENT RATING:1.5A
 - 1-3: CONTACT RESISTANCE: 40mΩ MAX.
 - 1-4: INSULATION RESISTANCE:500MΩ MIN.
 - 1-5: DIELECTRIC WITHSTANG VOLTAGE :1000V AC
 - 1-6: OPERAURE TEMPERATURE: -40℃~80℃



Recommend PCB Layout
(Jack Top View)
Tolerance: ±0.05mm

c	SHELL	1	BRASS	NI PLATING	
b	TERMINAL	8	PHOSPHOR BRONZE	Ø0.46mm	AU PLATING
a	HOUSING	1	PA9T UL94V-0	SEE TABLE1	
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES		SCALE:1/1	UNIT: mm	SIZE: A3	PAGE:1 OF 1	REV:A02	DWG.NO:
DECIMALS:	ANGLES:						
X : ±0.5	X : ±2°						
X.X : ±0.3	X.X : ±1°						
X.XX : ±0.2							

东莞市合陵电子有限公司
DongGuan Heling Electronic Co.,LTD

APPROVED BY
DICK

CHECKED BY
XSY

PREPARED BY
YST

CUSTOMER COPY