




RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.


REV.	ECN. NO.	APPD.



X	L	H
A	3.15	4.30
B	3.35	4.50
C	3.85	5.00
D	4.35	5.50
E	4.85	6.00
F	5.35	6.50
G	5.85	7.00
H	6.35	7.50
J	6.85	8.00
K	7.35	8.50
L	7.85	9.00
M	8.35	9.50
N	8.85	10.0



CIRCUIT DIAGRAM



PCB WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max. initial
Dielectric Strength	250 V AC(1mm)
Travel	0.25±0.1mm
Storage Temperature	-30° C to 85° C

Mechanical

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR
E	Button	PPA	1	Black
D	COVER	Brass	1	Cleaning
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag

Type	Operatin g Force(gf)		Heiht mm	Button	Leads Shape(G, J,T)	Ground pin (0,1)	Pre Optio n,1	
BTS0009	2	250±50	N	10.0	B (Black)	T	1 (Ground pin)	0 (Sum)
			M	9.5				
			L	9.0				
			K	8.5				
			J	8.0				
	1	160±50	H	7.5				
			G	7.0				
			F	6.5				
			E	6.0				
			D	5.5				
	0	100±30	C	5.0				
			B	4.5				
			A	4.3				

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Bozhong TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED.

X. ±0.50	X. ° ±2°	UNITS
.X ±0.30	.X° ±1°	mm
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		FINISH
		Q'TY

博众电气 东莞市博众电气有限公司 —BOZHONG ELECTRICAL— Dongguan Bozhong Electrical Co., Ltd	
PART NO. BTS0D009	TITLE: TACTILE SWITCH 6x6mm
APPD: ROGER	DWG NO.: BTS0D009
CHKD: ROC	SCALE SHEET REV. 1/1 1/1 A1
DR: BILLY WANG 2020/08/21	

Packaging:
1000 pieces for Bults