

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA6T+30%G. F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G. F UL94V-0, Color: Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact: Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Rating Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C



Ordering Information

F243-11 04 A0 B SU C 3

NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL:	PACKING
1-40P	Full of Gold	B: PA6T	A: PE Bag
	Semi-gold	C: PA6T	B: Tape & Reel
		D: LCP	C: Tube
			D: Tube+CAP
			E: Tray

A0=0.8u"	B0=0.8U"
A1=1u"	B1=1U"
A2=1.5u"	B2=1.5U"
A3=2u"	B3=2U"
A4=3u"	B4=3U"
A5=5u"	B5=5U"
A6=10u"	B6=10U"
A7=15u"	B7=15U"
A8=20u"	B8=20U"
A9=30u"	B9=30U"

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

RoHS COMPLIANT

客编: K2090

注意事项

1. 带*为品质重点检验尺寸

			OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司		
			X.X	±0.25	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
			X.XX	±0.20	SI ZE	A4	DESIGN		刘伟 2021.07.29	PART NO	F243-1104A0BSUC3
A0	2021.07.29	/	X.XXX	±0.10	SHEET		1/1	CHECK		TITLE: 2.0排母4.3mm塑高 1*4P 180度 DIP:2.7mm 底部带杠 U型 PA6T料 镀普金 144个/管	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		PROJ.	APPROVE	Cust order No.				