


Technical Data
 Material:
 Contact material:Brass
 Plating:Gold Flash
 Insulator material:Black polyester UL94V-0
 Standard:6T+30%G.F

Electrical:
 Current rating:1.5Amps/contact_max.
 Contact resistance:≤20mΩ/contact
 Insulation resistance:≥1000MΩ at V=100V
 Withstanding voltage:450V AC/minute

Mechanical:
 Soldering temperature:+260°C, 4s max
 UNSPECIFIED TOLERANCE: ±0.20



PCB Layout

$$A = 2.0 * \frac{nP}{2} \pm 0.40$$

$$B = 2.0 * \frac{nP}{2} - 2.0 \pm 0.20$$

Pin Number=2~80

APPROVALS		DATE	DRAWING NO.			
DRAWN	G.M.Chen	2015/7/17	D/2200W-22-XX-52			
CHECKED			SHEET 1 OF 1			
APPROVALS			PROJ.			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE: 30~80±, ±0.30 ANGLE 10~30 ±0.20 5~10 ±0.15 ±2° DRAWING NO.						