


环保物料

TEL:0769-82001899



*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over
Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO +105°C
CONTACT RESISTANCE:3Ω MAX.
INSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S

PIN ASSIGNMENT:

P1: 1 2 3 4 5 ● ● ● 49 50
P2: 1 2 3 4 5 ● ● ● 49 50

OF TRANSPORT DIVISION:

序号	名称	规格描述	数量
1	插头	IDC-50P 三件式 (2.54mm)	2
2	电线	UL2651 28AWG 1.27间距灰排 7/0.127TS	50P
3	卡扣	反扣50P (2.54mm)	2

TOLERANCE UNLESS OTHERWISE				DRAWN	CK tan
X.	±0.3	X°	±5°	CHKD	
.X	±0.20	.X°	±2°	APPD	
.XX	±0.08	.XX°	±1°	VIEW	⊕ ⊖
.XXX	±0.03	.XXX°	±0.5°		

XFCN 兴飞连接器有限公司
XFCN CONNECTORS CO., LTD.

PRODUCT NAME 灰排线两端IDC2.54/50P 三件式 L=200mm 不含插头
PART. NO. CL2542350200BC10E

SHEET	1/1
DATE	2023.7.5
UNITS	mm
SCALE	
DWG NO.	

MODIFICATION

DRAW

DATE