


环保物料

TEL:0769-82001899



*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over
Nickel Plated.

*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO +105°C
CONTACT RESISTANCE:3Ω MAX.
INSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S

PIN ASSIGNMENT:

P1:	1	2	3	4	5	●	●	●	39	40
P2:	1	2	3	4	5	●	●	●	39	40

OF TRANSPORT DIVISION:

序号	名称	规格描述	数量
1	插头	IDC-40P 三件式 (2.54mm)	2
2	电线	UL2651 28AWG 1.27间距灰排 7/0.127TS	40P
3	卡扣	反扣40P (2.54mm)	2

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan
				X.	±0.3	X°	±5°
				.X	±0.20	.X°	±2°
				.XX	±0.08	.XX°	±1°
				.XXX	±0.03	.XXX°	±0.5°
A0	MODIFICATION			DRAW	DATE		
AVR							

XFCN 兴飞连接器有限公司
XFCN CONNECTORS CO., LTD.

PRODUCT NAME 灰排线两端IDC2.54/40P 三件式 L=200mm 不含插头
PART. NO. CL2542340200BC10E

SHEET	1/1
DATE	2023.7.5
UNITS	mm
SCALE	
DWG NO.	