


环保物料

TEL:0769-82001899



*MATERIAL (IDC)
INSULATOR: PBT (UL 94V-0)
Contact: Copper Alloy.
Contact Plated: Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE: -20°C TO +105°C
CONTACT RESISTANCE: 3 Ω MAX.
INSULATION RESISTANCE: 5M Ω MIN.
WITHSTANDING VOLTAGE: 300V 10S

PIN ASSIGNMENT:

P1: 1 2 3 4 5 ● ● ● 59 60
P2: 1 2 3 4 5 ● ● ● 59 60

OF TRANSPORT DIVISION:

序号	名称	规格描述	数量
1	插头	IDC-60P 三件式 (2.54mm)	2
2	电线	UL2651 28AWG 1.27间距灰排 7/0.127TS	60P
3	卡扣	反扣60P (2.54mm)	2

TOLERANCE UNLESS OTHERWISE				DRAWN	CK tan
X.	±0.3	X°	±5°	CHKD	
.X	±0.20	.X°	±2°	APPD	
.XX	±0.08	.XX°	±1°	VIEW	⊕
.XXX	±0.03	.XXX°	±0.5°		
A0	MODIFICATION			DRAW	DATE
AVR					

XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO., LTD.		SHEET	1/1
		DATE	2023. 7. 5
		UNITS	mm
		SCALE	
PRODUCT NAME		灰排线两端IDC2.54/60P 三件式 L=200mm 不含插头	
PART. NO.		CL2542360200BC10E	
		DWG NO.	