




环保物料

TEL:0769-82001899



*MATERIAL (IDC)
INSULATOR: PBT (UL 94V-0)
Contact: Copper Alloy.
Contact Plated: Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE: -20°C TO +105°C
CONTACT RESISTANCE: 3Ω MAX.
INSULATION RESISTANCE: 5MΩ MIN.
WITHSTANDING VOLTAGE: 300V 10S

PIN ASSIGNMENT:



OF TRANSPORT DIVISION:

序号	名称	规格描述	数量
1	插头	IDC-12P 三件式 (2.54mm)	2
2	电线	UL2651 28AWG 1.27间距灰排 7/0.127TS	12P
3	卡扣	反扣12P (2.54mm)	2

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan
				X.	±0.3	X°	±5°
				.X	±0.20	.X°	±2°
				.XX	±0.08	.XX°	±1°
				.XXX	±0.03	.XXX°	±0.5°
A0	MODIFICATION			DRAW	DATE		
AVR				DRAW	DATE		

XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO., LTD.				SHEET	1/1
				DATE	2023. 7. 5
				UNITS	mm
				SCALE	
PRODUCT NAME				灰排线两端IDC2.54/12P 三件式 L=200mm 不含插头	
PART. NO.				CL2542312200BC10E	
VIEW				DWG NO.	