






环保物料

TEL: 0769-82001899





SPECIFICATIONS

- 1.Voltage rating: 50V AC, DC
 - 2.Current rating: 1A, AC, DC
 - 3.Withstanding Voltage: 500V AC/minute
 - 4.Insulation resistance:100M min
 - 5.Temperature range: -25 ° C--+85 ° C
 - 6.Contact resistance: 30m max
- WAFER
 Housing Material: PA9T/6T UL 94V0
 Pin Material: Phosphor Bronze or Brass
 Contact Area Plating: Plated Tin or Plated Gold
 Mates with :P1257 series Housing
 Poles:02-15P
 Part No.: M1257VS-xxP



Pin位数



PCB LAYOUT

编号	尺寸 (mm)		
	A	B	C
02	1.25	5.75	4.95
03	2.50	7.00	6.20
04	3.75	8.25	7.45
05	5.00	9.50	8.70
06	6.25	10.75	9.95
07	7.50	12.00	11.20
08	8.75	13.25	12.45
09	10.00	14.50	13.70
10	11.25	15.75	14.95
11	12.50	17.00	16.20
12	13.75	18.25	17.45
15	17.50	22.00	21.20

7A

2-6A

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO.,LTD.	SHEET	1/1	
				X.	±0.30	X°	±5°		CHKD	DATE	2020.04.12
				.X	±0.20	.X°	±2°		APPD	UNITS	mm
				.XX	±0.08	.XX°	±1°		VIEW	SCALE	1:1
AO	MODIFICATION	DRAW	DATE	.XXX	±0.03	.XXX°	±0.5°	PRODUCT NAME	1.25mm Crimp Style Connectors		
VER								PART. NO.	M1257VS-xxP		
1	2	3	4	5	6	7	8	9	10	DWG. NO.	009