


环保物料

TEL:0769-82001899



*MATERIAL (IDC)
INSULATOR: PBT (UL 94V-0)
Contact: Copper Alloy.
Contact Plated: Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE: -20°C TO +105°C
CONTACT RESISTANCE: 3 Ω MAX.
INSULATION RESISTANCE: 5M Ω MIN.
WITHSTANDING VOLTAGE: 300V 10S

PIN ASSIGNMENT:

P1: 1 2 3 4 5 ● ● ● 63 64
P2: 1 2 3 4 5 ● ● ● 63 64

OF TRANSPORT DIVISION:

序号	名称	规格描述	数量
1	插头	IDC-64P 三件式 (2.54mm)	2
2	电线	UL2651 28AWG 1.27间距灰排 7/0.127TS	64P
3	卡扣	反扣64P (2.54mm)	2

				TOLERANCE UNLESS OTHERWISE			
				X.	±0.3	X°	±5°
				.X	±0.20	.X°	±2°
AO				.XX	±0.08	.XX°	±1°
AVR	MODIFICATION		DRAW	DATE	.XXX	±0.03	.XXX° ±0.5°

XFCN 兴飞连接器有限公司
XFCN CONNECTORS CO., LTD.

PRODUCT NAME 灰排线两端IDC2.54/64P 三件式 L=200mm 不含插头
PART. NO. CL2542364200BC10E

SHEET	1/1
DATE	2023. 7. 5
UNITS	mm
SCALE	
DWG NO.	