



**SPECIFICATIONS**

Rated Current:3.0AMP  
 Contact Resistance:20mΩMax  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩMin  
 Operation Temperature:-40°c to +105°c

Contact Material: Brass  
 Contact Plating: Au Over Ni  
 Insulator Material: Polyester(UL94V-0)  
 Standard: PA66  
 Max.Processing Temp: 180°C for 30-60 seconds  
 (230°C for 10 seconds)



**Ordering Information**

HC-JP 254 - 1 - \*\* - OP - \* - \*\*

|                             |  |                             |   |  |
|-----------------------------|--|-----------------------------|---|--|
| No.of Rows<br>1=Single Type | Length<br>(mm)<br>45=4.5mm<br>60=6.0mm<br>65=6.5mm<br>135=13.5mm | Type<br>OP=Open<br>CL=Close | Color<br>B=Black<br>L=Blue<br>R=Red<br>W=White<br>Y=Yellow<br>V=Green | Contact Plating<br>G0:Gold Flash<br>G1:1u" Gold<br>G2:3u" Gold<br>G3:5u" Gold<br>G4:10u" Gold<br>G5:15u" Gold<br>G6:30u" Gold<br>S0:Gold Flash/Tin<br>S1:Tin |
|-----------------------------|--|-----------------------------|---|--|

|           |                        |                   |                   |                  |   |                          |             |     |
|-----------|------------------------|-------------------|-------------------|------------------|---|--------------------------|-------------|-----|
|           |                        |                   | GENERAL TOLERANCE | 制图<br>DRAWING    | <b>深圳市华灿天禄电子有限公司</b><br>ShenzhenhuacantianluELECTRONICS CO.,LTD |                          |             |     |
|           |                        |                   | DIM TOL           | 审核<br>CHECK      |   |                          |             |     |
|           |                        |                   | X.X ±0.30         | 批准<br>APPROVAL   | 产品名称<br>TITLE   | 2.54 跳线帽 黄色<br>(开口 加长带柄) | 版本<br>REV.  | A   |
|           |                        |                   | X.XX ±0.20        | 比例<br>SCALE      | 产品料号<br>PART NO.  | HC-JP254-1-135-OP-B-G1   | 单位<br>UNITS | mm  |
|           |                        |                   | X.XXX ±0.10       | 投影<br>Projection | 材料<br>MATERIAL  |                          |             |     |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE | Angle ±3.0°       |                  |   |                          | 页次<br>SHEET | 1/1 |