



Pushing Performance  
Since 1945

# SEK-18 SV MA STD STR29 60P PL2




Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 09 18 560 6924                                                                        |
| Specification      | SEK-18 SV MA STD STR29 60P PL2                                                        |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09185606924">https://b2b.harting.com/09185606924</a> |

## Identification

|                            |                |
|----------------------------|----------------|
| Category                   | Connectors     |
| Series                     | SEK Standard   |
| Element                    | Male connector |
| Description of the contact | Straight       |

## Version

|                    |                            |
|--------------------|----------------------------|
| Termination method | Wave soldering termination |
| Connection type    | PCB to cable               |
| Number of contacts | 60                         |
| Termination length | 2.9 mm                     |

## Technical characteristics

|                                    |                           |
|------------------------------------|---------------------------|
| Contact rows                       | 2                         |
| Contact spacing (termination side) | 2.54 mm                   |
| Rated current                      | 1 A                       |
| Insulation resistance              | $>10^9 \Omega$            |
| Contact resistance                 | $\leq 20 \text{ m}\Omega$ |
| Limiting temperature               | -55 ... +125 °C           |
| Insertion and withdrawal force     | $\leq 120 \text{ N}$      |
| Performance level                  | 2<br>acc. to IEC 60603-13 |
| Mating cycles                      | $\geq 250$                |
| Test voltage $U_{r.m.s.}$          | 1 kV                      |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                 |                               |
|-----------------|-------------------------------|
| Isolation group | IIIa ( $175 \leq CTI < 400$ ) |
|-----------------|-------------------------------|

## Material properties

|                                           |                                                                |
|-------------------------------------------|----------------------------------------------------------------|
| Material (insert)                         | Thermoplastic resin (PBT)                                      |
| Colour (insert)                           | Grey                                                           |
| Material (contacts)                       | Copper alloy                                                   |
| Surface (contacts)                        | Noble metal over Ni Mating side<br>Sn over Ni Termination side |
| Material flammability class acc. to UL 94 | V-0                                                            |
| RoHS                                      | compliant                                                      |
| ELV status                                | compliant                                                      |
| China RoHS                                | e                                                              |
| REACH Annex XVII substances               | Not contained                                                  |
| REACH ANNEX XIV substances                | Not contained                                                  |
| REACH SVHC substances                     | Not contained                                                  |
| California Proposition 65 substances      | Yes                                                            |
| California Proposition 65 substances      | Antimony trioxide                                              |
|                                           | Lead                                                           |
|                                           | Nickel                                                         |
| Requirement set with Hazard Levels        | R26                                                            |

## Specifications and approvals

|                        |                                   |
|------------------------|-----------------------------------|
| Specifications         | IEC 60603-13                      |
| UL / CSA               | UL 1977 ECBT2.E102079             |
|                        | CSA-C22.2 No. 182.3 ECBT8.E102079 |
| Railway classification | F3/I3                             |

## Commercial data

|                                |               |
|--------------------------------|---------------|
| Packaging size                 | 50            |
| Net weight                     | 16.78 g       |
| Country of origin              | Romania       |
| European customs tariff number | 85366990      |
| GTIN                           | 5713140035140 |
| ETIM                           | EC002637      |

## Commercial data

eCl@ss

27460201 PCB connector (board connector)

## Cross section of solder termination

