



Main

| | |
|-------------------|------------|
| Body type | Deep box |
| Device short name | AW |
| Series name | Heavy duty |

Complementary

| | |
|-------------------------------|-------------------------------|
| Line Rated Current | 10 A |
| Body material | Cast zinc |
| Contact form | Form ZZ DPDT-DB |
| Contact operation | Snap action |
| Contacts type and composition | 2 NO/2 NC |
| Fluid connection type | 0.5 inch BSP conduit entrance |
| Maximum displacement angle | 30 ° |
| Switch actuation | CCW |
| Tilting angle | 5 ° |
| Torque Value | 2.75 lbf.in (0.31 N.m) |
| Tripping angle | 2.5 ° |

Environment

| | |
|---------------------------------------|---|
| Ambient Air Temperature for Operation | -60...185 °F (-51...85 °C) |
| NEMA Degree of Protection | NEMA 1/2/4/12/13 |
| Product Certifications | CSA LR25490 class 3211 03[RETURN]CE[RETURN]UL listed file E42259 CCN NKCR |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10DS121496 |
| Discount Schedule | 0DS1 |
| GTIN | 785901443469 |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.70 in (4.318 cm) |
| Package 1 Width | 2.80 in (7.112 cm) |
| Package 1 Length | 5.20 in (13.208 cm) |
| Package 1 Weight | 20.00 oz (566.991 g) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|