



Main

Body type	Deep box
Device short name	AW
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Cast zinc
Cable entry	Conduit entry 1 0.79 in (20 mm)
Contact operation	Snap action
Maximum displacement angle	30 °
Mounting location	Front Rear
Switch actuation	CCW
Tilting angle	5 °
Torque Value	2.75 lbf.in (0.31 N.m)
Tripping angle	2.5 °
Type of operator	Momentary to be ordered separately

Environment

Ambient Air Temperature for Operation	-60...185 °F (-51...85 °C)
NEMA Degree of Protection	NEMA 1/2/4/12/13
Product Certifications	CSA LR25490 class 3211 03[RETURN]JUL listed file E42259 CCN NKCR[RETURN]CE

Ordering and shipping details

Category	US10DS121496
Discount Schedule	0DS1
GTIN	3389119056595
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.70 in (4.318 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	5.20 in (13.208 cm)
Package 1 Weight	20.00 oz (566.991 g)
Unit Type of Package 2	S02

Number of Units in Package 2	8
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	11.06 lb(US) (5.015 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------