

9002AW15

Foot Switch, Harmony, industrial, pedal and side shields, latch, 0.6A at 600 VAC, DPDT contact, NEMA 2, 4, 13 enclosure



Main

| | |
|-------------------------|---|
| Range | 9002AW |
| Product | Foot switch |
| Contact Operation | 1 step |
| Certifications | CSA UL Listed |
| Cable Entry | 0.75 inch NPT conduit entrance |
| Contact Arrangement | DPDT |
| Enclosure Rating | NEMA 2/4/13 |
| Voltage Rating | 600 V AC/DC |
| Protection | Side shield Pedal shield |
| Operator Action | Spring return with latch |
| Rated Breaking Capacity | 3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.75 A 480 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 3 A 120 V AC resistive control circuit UL 508 0.2 A 125 V DC resistive control circuit UL 508 |
| Height | 4.84 in (123 mm) |
| Width | 5.39 in (137 mm) |
| Depth | 9.02 in (229 mm) |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 21441-9002 AW FOOT SWITCHES |
| Discount Schedule | CS1 |
| GTIN | 785901817420 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 4.80 lb(US) (2.177 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 13.97 in (35.484 cm) |
| Package 1 width | 5.50 in (13.97 cm) |
| Package 1 Length | 35.48 in (90.129 cm) |

Offer Sustainability

| | |
|---------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |

| | |
|----------------------------|---|
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|
