



Main

| | |
|-------------------|------------|
| Device short name | C |
| Series name | Heavy duty |

Complementary

| | |
|-------------------------------|----------------------------|
| Line Rated Current | 10 A |
| Body material | Zinc alloy |
| Contacts material | Silver alloy (Ag/Ni) |
| Contact operation | Snap action |
| Contacts type and composition | 2 NO/2 NC switched neutral |
| Maximum displacement angle | 180 ° 90 ° |
| Specificity of operator | Standard pre-travel |
| Switch actuation | CW and CCW |
| Tilting angle | 10 ° |
| Torque Value | 4 lbf.in (0.45 N.m) |
| Tripping angle | 4 ° |

Environment

| | |
|---------------------------------------|--------------------------------|
| Ambient Air Temperature for Operation | -20...185 °F (-29...85 °C) |
| Product Certifications | UL Listed[RETURN]CE[RETURN]CSA |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10DS121499 |
| Discount Schedule | 0DS1 |
| GTIN | 785901974215 |
| Returnability | No |
| Country of origin | US |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 10.16 in (25.806 cm) |
| Package 1 Width | 4.00 in (10.16 cm) |
| Package 1 Length | 25.81 in (65.548 cm) |
| Package 1 Weight | 20.00 oz (566.99 g) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|