



Changeover operating mechanism for 3RT1481 and 3RT1482, AC (50...60 Hz) / DC operation, 100 ... 127 V AC / 100 ... 110 V DC

General technical data			
product brand name		SIRIUS	
product designation		Magnet coil	
Control circuit			
type of voltage of the control supply voltage		AC/DC	
control supply voltage			
• 1 at AC			
— at 50 Hz rated value			
— at 60 Hz rated value			
• 2 at AC			
— at 50 Hz rated value		100 V	
— at 60 Hz rated value		100 V	
control supply voltage			
• 1 at DC rated value		127 V	
• 2 at DC rated value		127 V	
operating range factor control supply voltage rated value of magnet coil at AC			
• at 50 Hz		0.85 ... 1.1	
• at 60 Hz		0.85 ... 1.1	
Certificates/ approvals			
General Product Approval		EMC	Declaration of Conformity
			Test Certificates

[Confirmation](#)



[Special Test Certificate](#)

Marine / Shipping

other

Railway



[Confirmation](#)

[Miscellaneous](#)

[Special Test Certificate](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT1982-5AF31>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT1982-5AF31>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT1982-5AF31>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT1982-5AF31&lang=en

last modified:

1/12/2021 