



Main

Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Localisation on device	Viton seal kit
Operating Distance	0.25 inch
Operating force	3 lbf
Operating travel	0.02 in (0.51 mm) 0.08 in (2.03 mm)
Switch actuation	Horizontal

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
Product Certifications	UL Listed[RETURN]CSA[RETURN]CE

Ordering and shipping details

Category	US10DS121499
Discount Schedule	0DS1
GTIN	785901915560
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.16 in (33.419 cm)
Package 1 Width	5.18 in (13.157 cm)
Package 1 Length	33.42 in (84.885 cm)
Package 1 Weight	20.00 oz (566.99 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------