

Product data sheet

Characteristics

9007AW36M11

Limit switch, 9007, 600 VAC 15amp aw
+options



Main

Body type	Plug-in
Device short name	AW
Series name	Heavy duty

Complementary

Line Rated Current	15 A
Body material	Cast zinc
Cable entry	Conduit entry 1 0.79 in (20 mm)
Contact operation	Snap action
Impregnation material	Oil
Mounting location	Front Rear
Operating Distance	0.19...0.31 inch
Operating travel	0.09 in (2.29 mm) 0.05 in (1.27 mm)
Size	Roller 0.63 x 0.25 inch
Switch actuation	Horizontal
Torque Value	3 lbf.in (0.34 N.m)
Type of operator	Spring return roller

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
NEMA Degree of Protection	NEMA 1/2/4/12/13
Product Certifications	CE[RETURN]JUL listed file E42259 CCN NKCR[RETURN]CSA LR25490 class 3211 03

Ordering and shipping details

Category	US10DS121496
Discount Schedule	0DS1
GTIN	785901101697
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.78 in (45.161 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	45.16 in (114.709 cm)
Package 1 Weight	20.00 oz (566.991 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------