

Product data sheet

Characteristics

9007AW32M11

Limit switch, 9007, 600 VAC 15amp aw
+options



Main

| | |
|-------------------|------------|
| Body type | Standard |
| Device short name | AW |
| Series name | Heavy duty |

Complementary

| | |
|-----------------------|--|
| Line Rated Current | 15 A |
| Body material | Cast zinc |
| Cable entry | Conduit entry 1 0.79 in (20 mm) |
| Contact operation | Snap action |
| Impregnation material | Oil |
| Mounting location | Front Rear |
| Operating Distance | 0.19...0.31 inch |
| Operating travel | 0.05 in (1.27 mm) 0.09 in (2.29 mm) |
| Size | Roller 0.63 x 0.25 inch |
| Switch actuation | Horizontal |
| Torque Value | 3 lbf.in (0.34 N.m) |
| Type of operator | Spring return roller |

Environment

| | |
|---------------------------------------|--|
| Ambient Air Temperature for Operation | 0...185 °F (-18...85 °C) |
| NEMA Degree of Protection | NEMA 1/2/4/12/13 |
| Product Certifications | CSA LR25490 class 3211 03[RETURN]UL listed file E42259 CCN NKCR[RETURN]CE |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10DS121496 |
| Discount Schedule | 0DS1 |
| GTIN | 785901101550 |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.70 in (4.318 cm) |
| Package 1 Width | 2.80 in (7.112 cm) |
| Package 1 Length | 5.20 in (13.208 cm) |
| Package 1 Weight | 20.00 oz (566.991 g) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|