



Main

Device short name	C
Head type	Type T/FT turret head rotary lever
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	A600 R300
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Specificity of operator	Standard pre-travel First stage : 10° - second stage : 2.5°
Switch actuation	CW and CCW
Torque Value	4 lbf.in (0.45 N.m)
Tripping angle	4 °
Type of operator	Drive shaft with T-FT hub

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Environmental characteristic	Hazardous location
Product Certifications	CSA[RETURN]CE[RETURN]UL Listed

Ordering and shipping details

Category	US10DS121499
Discount Schedule	ODS1
GTIN	785901348368
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.99 in (17.742 cm)
Package 1 Width	2.75 in (6.985 cm)
Package 1 Length	17.74 in (45.064 cm)
Package 1 Weight	2.50 lb(US) (1.134 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------