



Main

Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	180 °
Operating Distance	0.25 inch
Operating force	4 lbf
Operating travel	0.08 in (2.03 mm) 0.03 in (0.76 mm)
Switch actuation	Horizontal
Type of operator	Side plunger

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
Product Certifications	UL Listed[RETURN]CE[RETURN]CSA

Ordering and shipping details

Category	US10DS121499
Discount Schedule	0DS1
GTIN	785901724810
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.99 in (7.6 cm)
Package 1 Width	3.70 in (9.4 cm)
Package 1 Length	6.50 in (16.5 cm)
Package 1 Weight	23.36 oz (662.2 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------