

Main

Device Application	Earth moving equipment General transportation Machine tools
Device short name	MS

Complementary

Line Rated Current	10 A
Body material	Cast zinc
Cable entry	Side entry
Cable length	12 ft (3.66 m)
Contact form	Form C SPDT
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Electrical connection	AWG 18 SJTO cable Black)
Material	Stainless steel: roller
Mounting support	shoulder
Operating force	80 ozf
Permissible voltage	28 V DC
Size	Roller 0.5 "
Switch actuation	Horizontal
Type of operator	Spring return roller

Environment

Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)
IP Degree of Protection	IP67
NEMA Degree of Protection	NEMA 1/2/4/6/6P/12/13
Product Certifications	CSA[RETURN]UL Listed[RETURN]CE
Shock resistance	35 gn
Vibration resistance	10 gn 75...1200 Hz)

Ordering and shipping details

Category	US10DS122431
Discount Schedule	0DS1
GTIN	785901153672
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.81 in (9.677 cm)
Package 1 Width	1.50 in (3.81 cm)
Package 1 Length	9.68 in (24.581 cm)
Package 1 Weight	19.20 oz (544.311 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations