



### Main

Device short name	C
Head type	Type C turret head rotary lever
Provided equipment	Receptacle
Series name	Heavy duty

### Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Cable entry	0.5 in (12.70 mm) NPT conduit entry
Contact code designation	A600 R300
Contact form	Form ZZ DPDT-DB
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Contacts type and composition	2 NO/2 NC
Maximum displacement angle	90 °
Pilot light	Without pilot lamp
Switch actuation	CW and CCW
Tilting angle	45 °
Torque Value	3 lbf.in (0.34 N.m)

### Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Environmental characteristic	Hazardous location
Product Certifications	UL Listed[RETURN]CE[RETURN]CSA

### Ordering and shipping details

Category	US10DS121499
Discount Schedule	ODS1
GTIN	785901711551
Returnability	No
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.99 in (17.742 cm)
Package 1 Width	2.75 in (6.985 cm)
Package 1 Length	17.74 in (45.064 cm)
Package 1 Weight	2.50 lb(US) (1.134 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------