



coupling link 24 V DC, screw terminal, for front-side mounting to contactors 3RT2 and auxiliary contactors 3RH2

product brand name	SIRIUS
product category	Coupling links
product designation	Coupling link
General technical data	
size of contactor	S00, S0, S2, S3
product component protective wiring	Yes
insulation voltage rated value	300 V
degree of pollution	3
protection class IP on the front	IP20
Substance Prohibitance (Date)	07/01/2006
SVHC substance name	Blei - 7439-92-1 Bleimonoxid (Bleioxid) - 1317-36-8
type of voltage of the control supply voltage	DC
control supply voltage 1	
• at DC rated value	24 V
operating range factor control supply voltage rated value of magnet coil at DC	
• initial value	0.7
• full-scale value	1.25
number of NO contacts for auxiliary contacts instantaneous contact	1
operational current of auxiliary contacts at AC-12	
• at 24 V	6 A
• at 230 V	6 A
operational current of auxiliary contacts at AC-15	
• at 24 V	3 A
• at 230 V	3 A
operational current of auxiliary contacts at DC-13	
• at 24 V	1 A
• at 110 V	0.2 A
• at 220 V	0.1 A
Ambient conditions	
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
Installation/ mounting/ dimensions	
mounting position	any
fastening method	direct mounting
height	35 mm
width	45 mm
depth	50 mm

connectable conductor cross-section for auxiliary contacts	
• solid or stranded	0.5 ... 2.5 mm ²
• finely stranded with core end processing	0.5 ... 1.5 mm ²
type of connectable conductor cross-sections	
• for auxiliary contacts	
— solid	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
— finely stranded with core end processing	2x (0.5 ... 1.5 mm ²)

Approvals Certificates

General Product Approval	EMV	Test Certificates
--------------------------	-----	-------------------



[Confirmation](#)



[Type Test Certificates/Test Report](#)

Marine / Shipping



Marine / Shipping

other



[Miscellaneous](#)

[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RH2914-1GP11>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RH2914-1GP11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RH2914-1GP11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RH2914-1GP11&lang=en



