



Main

Body type	Standard plug-in
Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	Q600 A600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Mounting location	Front Rear
Switch actuation	Any direction
Tilting angle	10 °
Torque Value	3 lbf.in (0.34 N.m)
Tripping angle	3 °
Type of operator	Spring return wobble stick Delrin extension

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
NEMA Degree of Protection	NEMA 1/2/4/6/6P/12/13
Product Certifications	CE[RETURN]UL listed file E42259 CCN NKCR[RETURN]CSA LR25490 class 3211 03

Ordering and shipping details

Category	US10DS121499
Discount Schedule	0DS1
GTIN	785901895688
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	20.00 oz (566.991 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------