


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING-DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
2. MATERIAL:
 - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	接头	三代IPEX端子	1
①	同轴线	RG0.81 蓝色线, OD:0.81MM	AS

深圳市金航标电子有限公司


www.kinghelm.com.cn

KH-IPEX3-221-RG0.81-BU250

0755-28190160

ALL DIMENSION ARE IN MM	DRAWN	Jamy	DATE	2020-06-15
	ENG.			
COMPUTER GENERATED IN SOLIDWORKS	MFG.			
DO NOT SCALE THIS DRAWING	Q.A.			

三代IPEX TO OPEN RG0.81蓝色转接线



PROJECTION
GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX
± 1° ± 0.3 ± 0.25 ± 0.150

SIZE	Number	REV
B		A
SCALE: Free	TYPE	SHEET 1 OF 1

CUSTOMER PIN: