

HC-D25-SP-RBK - Profile gasket



1414672

<https://www.phoenixcontact.com/us/products/1414672>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement profile gasket, for HC-EVO-D25.....BK housing



Commercial data

Item number	1414672
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF66
Product key	BF7APZ
Catalog page	Page 652 (C-4-2015)
GTIN	4055626031231
Weight per piece (including packing)	3.03 g
Weight per piece (excluding packing)	3.03 g
Customs tariff number	40169300
Country of origin	IT

HC-D25-SP-RBK - Profile gasket

1414672

<https://www.phoenixcontact.com/us/products/1414672>




Technical data

Product properties

Type	D25
Product type	Seal

Dimensions

Dimensional drawing	
Width	30 mm
Height	4 mm
Length	80 mm

Material specifications

Seal material Profile gasket	NBR
------------------------------	-----

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Assembly instructions	The replacement seal should be bonded with Loctite 454 adhesive.
	For HC-EVO-D25....BK housing

HC-D25-SP-RBK - Profile gasket


1414672

<https://www.phoenixcontact.com/us/products/1414672>



Drawings

Dimensional drawing



Dimensional drawing

HC-D25-SP-RBK - Profile gasket



1414672

<https://www.phoenixcontact.com/us/products/1414672>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414672>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-D25-SP-RBK - Profile gasket



1414672

<https://www.phoenixcontact.com/us/products/1414672>

Classifications

ECLASS

ECLASS-11.0	23071590
ECLASS-12.0	23071590
ECLASS-13.0	23071590

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	31401600
-------------	----------

HC-D25-SP-RBK - Profile gasket



1414672

<https://www.phoenixcontact.com/us/products/1414672>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com