

A 25 -32 - Ferrule



1090636

<https://www.phoenixcontact.com/us/products/1090636>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, color: silver

Commercial data

Item number	1090636
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH3412
Catalog page	Page 480 (C-3-2019)
GTIN	4055626901268
Weight per piece (including packing)	1.449 g
Weight per piece (excluding packing)	1.4 g
Customs tariff number	85369010
Country of origin	DE

A 25 -32 - Ferrule



1090636
<https://www.phoenixcontact.com/us/products/1090636>

Technical data

Notes

General	These ferrules are not included in DIN 46228-1: 1992-08
---------	---


Product properties

Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M

Connection data

Conductor connection	
Conductor cross section flexible max.	25 mm²
Conductor cross section AWG max.	4
Stripping length	32 mm

Dimensions

Dimensional drawing	
Maximum stripping length	32 mm
Ferrule diameter	7.3 mm
Sleeve wall thickness	0.2 mm
Inner dimensions of the insulating collar	9.5 mm

Material specifications

Color	silver
Material	CU-DHP
Coating	tin-plated (galvanic)

Environmental and real-life conditions

Ambient conditions	
Permanent temperature	105 °C
Short-term temperature	120 °C

Standards and regulations

Design according to standard	DIN 46228-1, UL 486F-A
------------------------------	------------------------

A 25 -32 - Ferrule


1090636

<https://www.phoenixcontact.com/us/products/1090636>



Drawings

Dimensional drawing



Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

A 25 -32 - Ferrule




1090636


<https://www.phoenixcontact.com/us/products/1090636>

Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1090636>



UL Listed
Approval ID: E488001



cUL Listed
Approval ID: E488001



cULus Listed
Approval ID: E488001

cULus Listed

A 25 -32 - Ferrule



1090636

<https://www.phoenixcontact.com/us/products/1090636>

Classifications

ECLASS

ECLASS-11.0	27400201
ECLASS-13.0	27400201
ECLASS-12.0	27400201

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

A 25 -32 - Ferrule



1090636

<https://www.phoenixcontact.com/us/products/1090636>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

A 25 -32 - Ferrule

1090636

<https://www.phoenixcontact.com/us/products/1090636>



Accessories

CRIMPFOX 25R - Crimping pliers

1212039

<https://www.phoenixcontact.com/us/products/1212039>



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 10 mm² ... 25 mm², lateral entry, WM crimp

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com