

CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos. : 16, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 6 mm ... 10 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1243756

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1619704
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABRAEA
GTIN	4046356822114
Weight per piece (including packing)	92.533 g
Weight per piece (excluding packing)	83.3 g
Customs tariff number	85366990
Country of origin	DE

CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Technical data

Notes

General	Order 6 x Ø 1 mm crimp contacts separately
---------	--

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Note	Order information: Order 6 x Ø 1 mm crimp contacts separately
Coding	N
Insulation body material	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	16
Direction of rotation	Standard
Connection profile	16
Contact diameter	1 mm
Litz wire cross-section	0.08 mm ²
Litz wire cross-section	1 mm ²
Nominal current per signal contact	8 A
Rated voltage Signal contact	48 V AC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	6 mm ... 10 mm
Seal material	NBR

Environmental and real-life conditions

CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CA-16S1N8A8007 - Cable connector




1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Drawings

Dimensional drawing



Technical drawings can be found under Downloads

CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1619704>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	3 A	- 20	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	5 A	- 20	-

cULus Recognized				
-------------------------	--	--	--	--

CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

Accessories

RC-11S2000 - Crimp contact

1596772

<https://www.phoenixcontact.com/pc/products/1596772>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.08 mm² ... 0.22 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241093

RC-12S2000 - Crimp contact

1599600

<https://www.phoenixcontact.com/pc/products/1599600>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.14 mm² ... 0.56 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241093

CA-16S1N8A8007 - Cable connector

1619704

<https://www.phoenixcontact.com/pc/products/1619704>



RC-1KS2000 - Crimp contact

1602998

<https://www.phoenixcontact.com/pc/products/1602998>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.5 mm² ... 1 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1241572

CA-Z0077 - Metal protective cap

1627224

<https://www.phoenixcontact.com/pc/products/1627224>



Metal protective cap, degree of protection: IP67, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1245447

CA-16S1N8A8007 - Cable connector

1619704

<https://www.phoenixcontact.com/pc/products/1619704>



SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/pc/products/1607456>

Torque screwdriver, series: RC



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/pc/products/1607455>

Hook wrench, series: RC



CA-16S1N8A8007 - Cable connector



1619704

<https://www.phoenixcontact.com/pc/products/1619704>

RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/pc/products/1620588>

Color coding, color: green



RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/pc/products/1620592>

Color coding, color: orange



CA-16S1N8A8007 - Cable connector

1619704

<https://www.phoenixcontact.com/pc/products/1619704>



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/pc/products/1620593>

Color coding, color: black



RF-Z0003 - Square mounting flange

1607905

<https://www.phoenixcontact.com/pc/products/1607905>



Square mounting flange, Axial seal, 4xM3, flange dimensions: 35 mm x 35 mm, series: RF, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1242369

CA-16S1N8A8007 - Cable connector

1619704

<https://www.phoenixcontact.com/pc/products/1619704>



RC-22S2000 - Crimp contact

1603327

<https://www.phoenixcontact.com/pc/products/1603327>



Crimp contact, Socket, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.22 mm² ... 0.56 mm², Single contact, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb <0.1%)

RC-22S2400 - Crimp contact

1603332

<https://www.phoenixcontact.com/pc/products/1603332>



Crimp contact, Socket, rolled, Taped product, number of pieces per reel: 10000, contact diameter: 1 mm, crimp range: 0.22 mm² ... 0.56 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb <0.1%)

CA-16S1N8A8007 - Cable connector

1619704

<https://www.phoenixcontact.com/pc/products/1619704>



RC-22S2300 - Crimp contact

1603330

<https://www.phoenixcontact.com/pc/products/1603330>



Crimp contact, Socket, rolled, Taped product, number of pieces per reel: 500, contact diameter: 1 mm, crimp range: 0.22 mm² ... 0.56 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb <0.1%)

PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/pc/products/1577206>



Plastic protective cap, M23, degree of protection: IP20, series: CA

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com