

# PTFIX-NS35A-FIX - DIN rail adapter



3274057

<https://www.phoenixcontact.com/us/products/3274057>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter, with end stop function, depth: 12 mm, width: 10.3 mm, height: 45.7 mm, color: gray, mounting type: NS 35/7,5



## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3274057             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 20 pc               |
| Sales key                            | BE09                |
| Product key                          | BEAZ11              |
| Catalog page                         | Page 438 (C-1-2019) |
| GTIN                                 | 4055626394138       |
| Weight per piece (including packing) | 1.633 g             |
| Weight per piece (excluding packing) | 1.576 g             |
| Customs tariff number                | 39269097            |
| Country of origin                    | PL                  |

# PTFIX-NS35A-FIX - DIN rail adapter



3274057

<https://www.phoenixcontact.com/us/products/3274057>

## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

### Dimensions

|                    |         |
|--------------------|---------|
| Width              | 10.3 mm |
| Height             | 45.7 mm |
| Depth              | 12 mm   |
| Depth on NS 35/7,5 | 13.7 mm |
| Depth on NS 35/15  | 21.2 mm |

### Material specifications

|                                        |      |
|----------------------------------------|------|
| Color                                  | gray |
| Flammability rating according to UL 94 | V0   |

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

### Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# PTFIX-NS35A-FIX - DIN rail adapter



3274057

<https://www.phoenixcontact.com/us/products/3274057>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3274057>



LR

Approval ID: LR2002627TA

# PTFIX-NS35A-FIX - DIN rail adapter



3274057

<https://www.phoenixcontact.com/us/products/3274057>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27370419 |
| ECLASS-12.0 | 27370419 |
| ECLASS-13.0 | 27370419 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001024 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTFIX-NS35A-FIX - DIN rail adapter



3274057

<https://www.phoenixcontact.com/us/products/3274057>

## Environmental product compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)