


Kinghelm®

| REVISIONS | | | | | |
|-----------|--------|-------------|-----|-----|------|
| REV | NUMBER | DESCRIPTION | DWN | CHK | DATE |
| A | | DESIGN | | | |



- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
 - MATERIAL:
 - SEE TABLE
 - ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION | QTY. |
|----------|-------------|-----------------------|------|
| ② | 接头 | 一代IPEX端子 | 1 |
| ① | 同轴线 | RG0.81白色线, OD: 0.81mm | AS |

深圳市金航标电子有限公司 www.kinghelm.com.cn

KH-IPEX-221-RG0.81-WH300 0755-28190160

| | | | |
|----------------------------------|---------------|--------------------|----------------------------|
| ALL DIMENSION ARE IN MM | DRAWN Jamy | DATE 2020-06-15 | 一代IPEX TO OPEN RG0.81白色转接线 |
| | ENG. | | |
| COMPUTER GENERATED IN SOLIDWORKS | MFG. | | |
| DO NOT SCALE THIS DRAWING | Q.A. | | |

CUSTOMER PIN:

| | | | |
|-------------|--|-------------------------|-----------------|
| PROJECTION | GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150 | SIZE Number B | REV A |
| SCALE: Free | | TYPE | SHEET 1 OF 1 |