

CUC-PPC-A2RBK-PC - Protective cover



1424989

<https://www.phoenixcontact.com/us/products/1424989>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover, degree of protection: IP65, number of positions: 2



Commercial data

Item number	1424989
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOJZ
Catalog page	Page 364 (C-2-2019)
GTIN	4055626386591
Weight per piece (including packing)	10.7 g
Weight per piece (excluding packing)	10.7 g
Customs tariff number	85389099
Country of origin	DE

CUC-PPC-A2RBK-PC - Protective cover



1424989

<https://www.phoenixcontact.com/us/products/1424989>

Technical data

Product properties

Product type	Data plug
Number of positions	2

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Dimensions

Width	22 mm
Height	55.7 mm
Depth	21 mm
Length	34 mm

Material specifications

Material	Plastic
Flammability rating according to UL 94	V0
Seal material	NBR
	NBR
Locking latch material	PA

Cable/line

External cable diameter ()	4.5 mm ... 8 mm
Cable cross section	0.14 mm ²

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

CUC-PPC-A2RBK-PC - Protective cover



1424989

<https://www.phoenixcontact.com/us/products/1424989>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440208

ETIM

ETIM 8.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-PPC-A2RBK-PC - Protective cover



1424989

<https://www.phoenixcontact.com/us/products/1424989>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

CUC-PPC-A2RBK-PC - Protective cover

1424989

<https://www.phoenixcontact.com/us/products/1424989>



Accessories

VS-PPC-C2-MSTB-MNNA-P13-A5-SP - Power connector

1608074

<https://www.phoenixcontact.com/us/products/1608074>



Power connector, degree of protection: IP65, number of positions: 5, material: Zinc die-cast, connection method: Spring-cage connection, connection cross section: AWG 18- 13, cable outlet: straight, color: silver

CUC-V14-F2ZNI-EM/24FN5:FC - Panel feed-through

1408235

<https://www.phoenixcontact.com/us/products/1408235>



Push/pull panel mounting frame, metal, version 14, including contact insert with spring-cage connection, flexible coding, for rectangular mounting cutout, with seal, without fixing screws

CUC-PPC-A2RBK-PC - Protective cover

1424989

<https://www.phoenixcontact.com/us/products/1424989>



VS-PPC-F2-MSTB-MNNA-1R-P - Panel mounting frames

1608087

<https://www.phoenixcontact.com/us/products/1608087>



MSTB panel mounting frame, IP67, for push-pull interlocking, metal, for PCB connection, for square panel cutout, with grommet, without mounting screws

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com