

PTFIX 10/S-F - Flange

1082917

<https://www.phoenixcontact.com/us/products/1082917>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flange, with screw-on fixing, depth: 25.1 mm, width: 8.6 mm, height: 37 mm, color: gray

Commercial data

Item number	1082917
Packing unit	1 pc
Minimum order quantity	20 pc
Sales key	BE09
Product key	BEAZ11
GTIN	4055626817033
Weight per piece (including packing)	4.3 g
Weight per piece (excluding packing)	4.35 g
Customs tariff number	85389099
Country of origin	PL

PTFIX 10/S-F - Flange

1082917

<https://www.phoenixcontact.com/us/products/1082917>



Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	8.6 mm
Height	37 mm
Depth	25.1 mm

Material specifications

Color	gray
Material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

PTFIX 10/S-F - Flange

1082917

<https://www.phoenixcontact.com/us/products/1082917>



Classifications

ECLASS

ECLASS-11.0	27370419
ECLASS-12.0	27370419
ECLASS-13.0	27250302

ETIM

ETIM 9.0	EC001024
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PTFIX 10/S-F - Flange



1082917
<https://www.phoenixcontact.com/us/products/1082917>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com