






RoHS



- 技术参数
1. 做用温度: -25~+85℃;
 2. 额定负荷: DC 12V 50mA;
 3. 接触电阻: ≤30mΩ;
 4. 绝缘电阻: ≥100MΩ;
 5. 耐 压: AC250V(50Hz)/min;
 6. 动 作 力: 260±50gf;
 7. 使用寿命: 5~7万次;
 8. 开关的行程尺寸为0.25mm±0.1mm
 9. 开关外观应无破裂、无损伤。
 10. 动作应灵活, 无卡住现象, 电路转换正常。

单位: mm		对应尺寸			
型号	H	L	型号	H	L
TC-6615K-4.3	4.3	3.15	TC-6615K-12.5	12.5	11.35
TC-6615K-4.5	4.5	3.35	TC-6615K-13.0	13.0	11.85
TC-6615K-5.0	5.0	3.85	TC-6615K-13.5	13.5	12.35
TC-6615K-5.5	5.5	4.35	TC-6615K-14.0	14.0	12.85
TC-6615K-6.0	6.0	4.85	TC-6615K-14.5	14.5	13.35
TC-6615K-6.5	6.5	5.35	TC-6615K-15.0	15.0	13.85
TC-6615K-7.0	7.0	5.85	TC-6615K-15.5	15.5	14.35
TC-6615K-7.5	7.5	6.35	TC-6615K-16.0	16.0	14.85
TC-6615K-8.0	8.0	6.85	TC-6615K-16.5	16.5	15.35
TC-6615K-8.5	8.5	7.35	TC-6615K-17.0	17.0	15.85
TC-6615K-9.0	9.0	7.85	TC-6615K-18.0	18.0	16.85
TC-6615K-9.5	9.5	8.35	TC-6615K-19.0	19.0	17.85
TC-6615K-10.0	10.0	8.85	TC-6615K-20.0	20.0	18.85
TC-6615K-10.5	10.5	9.35	TC-6615K-21.0	21.0	19.85
TC-6615K-11.0	11.0	9.85	TC-6615K-22.0	22.0	20.85
TC-6615K-11.5	11.5	10.35	TC-6615K-23.0	23.0	21.85
TC-6615K-12.0	12.0	10.85	TC-6615K-29.0	29.0	27.85



CAD设计		ZC-HJ-151										
		机架		1	铁皮 T=0.5	Cu/Ep: CuSn2						
CAD绘图		6										
		5	嵌件	1	H62Y T=0.3	Cu/Ep: Ag2		更改文件				
旧底图总号		4	底座	1	PPA 黑色			设计	王振钊	17.06.13		
		3	簧片	1	复银铜带 T=0.1	借用作件		审核	李攀进	17.06.13		
签 字		2	盖板	1	冷轧钢带 T=0.3	借用作件		工 艺				
日 期		1	帽头	1	PPA 黑色	借用作件		标准化				
序 号		1	帽头	1	PPA 黑色	借用作件		批 准	罗观彬	17.06.13		
				数量	材 料	附 注						
								</				