

T495X227M010ZTA1007280

Obsolete

B45197A, Tantalum, MnO2 Tantalum, 220 uF, 20%, 10 VDC, SMD, Molded, Low ESR, Surge Robust, 100 mOhms, 7343, Height Max = 4.4mm



Dimensions	
Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	4.1mm +/-0.3mm
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
K	1.8mm TYP

Packaging Specifications	
Packaging	T&R, 330mm
Packaging Quantity	4750

General Information	
Series	B45197A
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, Molded, Low ESR, Surge Robust
Features	Low ESR, Surge Robust, Automotive
RoHS	Yes
Termination	Tin
AEC-Q200	No
Notes	Obsolete.

Specifications	
Capacitance	220 uF
Capacitance Tolerance	20%
Voltage DC	10 VDC (85C), 6.7 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	10%
Failure Rate	N/A
Resistance	0.1 Ohms (100kHz)
Ripple Current	1280 mAmps (25C), 1152 mAmps (85C), 512 mAmps (125C)
Leakage Current	22 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.