

**BU-P1581-@**  
(Panel Mount Banana Jack)



- Mueller's BU-P1581 is a Banana Jack that mounts into panels ranging in thickness from 0.063" (1.6mm) to 0.375" (9.5mm).
- Material:
  - Body – Nickel plated Brass
  - Insulator – Polycarbonate
  - Lock Washer – Nickel plated Steel
  - Hex Nut – Nickel plated Brass
- Ratings:
  - Operating Temperature: 115°C (239°F)
  - For personal safety, do not hold when voltages exceed 30 Vrms/60 Vdc.
  - Hands free use up to 2500 WVDC
  - Current – 15 Amps
- Color: The "@" in the model number represents color. Available colors:
  - 0 Black, -2 Red,
- RoHS 3 Compliant