

Data sheet

27119.1 PAPIKD 2,5 GN



End plate, Width: 1.5 mm, Colour: Beige

Business data

Article number	27119.1
Article name	PAPIKD 2,5 GN
GTIN (EAN)	4044211227319
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	5.2 g
Weight per piece (including packaging)	5.4 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	27119.6
Product description	End plate

Data sheet

27119.1 PAPIKD 2,5 GN



Technical data

Dimensions

Length	102 mm
Width	1.5 mm
Height	56.2 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C


Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media


Accessories

##INVERSE##CONTA-CONNECT



Three-level initiator terminal | Multi-wire terminal,Push-in-connection, Mounting type:
Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5,1 mm, Colour: Grey


Article number	Article name	GTIN (EAN)	Packaging unit
<u>27039.6</u>	PIKD 2,5 GR	4044211227210	50



Three-level initiator terminal |Multi-wire terminal, Push-in connection, Mounting type:
Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27041.6</u>	PIKD 2,5/SV GR	4044211227241	50

##INVERSE##CONTA-CONNECT



Three-level initiator terminal |Multi-wire terminal, Push-in connection, Mounting type:
Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27041.6</u>	PIKD 2,5/SV GR	4044211227241	50