

Data sheet

2957.3 TWMF OG



Partition plate, Width: 2 mm, Colour: Orange

Business data

Article number	2957.3
Article name	TWMF OG
GTIN (EAN)	4044211056865
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	10 g
Weight per piece (including packaging)	10.5 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2957.2
Product description	Partition plate

Data sheet

2957.3 TWMF OG

Technical data

Dimensions

Length	88 mm
Width	2 mm
Min. thickness	2 mm
Height	68.5 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

Protective hood



Cover profile, Length: 90 mm, Width: 1000 mm, Colour: Transparent

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2958.2</u>	AD 3/1000 mm transparent	4044211056889	1 M