

Data sheet

3760.3 ZAP 6/2A OG



End plate, Width: 2 mm, Colour: Orange

Business data

Article number	3760.3
Article name	ZAP 6/2A OG
GTIN (EAN)	4044211060824
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	3.8 g
Weight per piece (including packaging)	3.9 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	3760.2
Product description	End plate

Technical data

Dimensions

Length	65 mm
Width	2 mm
Height	40 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

##INVERSE##CONTA-CONNECT



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3589.2</u>	ZSL 6/2A GNYE	4044211151973	100 ST



Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1725.2</u>	ZSL 6/2A Ex GNYE	4044211059453	100 ST



Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1719.2</u>	ZRK 6/2A Ex BG	4044211059279	100



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3581.2</u>	ZRK 6/2A BG	4044211151867	100