


Data sheet

2762.3 AP 10 OG



End plate, Width: 2 mm, Colour: Orange

Business data

Article number	2762.3
Article name	AP 10 OG
GTIN (EAN)	4044211107703
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	2.85 g
Weight per piece (including packaging)	2.9 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2762.2
Product description	End plate

Data sheet

2762.3 AP 10 OG

Technical data

Dimensions

Length	60.49 mm
Width	2 mm
Min. thickness	2 mm
Height	33.8 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media


Accessories

##INVERSE##CONTA-CONNECT




Fuse-disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1104.2</u>	SIK 10/LED(RD)/20-30V DC/40-60V AC BG	4044211016753	25 ST




Fuse-disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1103.2</u>	SIK 10/LED(RD)/12V DC/24V AC BG	4044211016548	25 ST




Fuse-disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1105.2</u>	SIK 10/LED(RD)/40-60V DC/80-120V AC BG	4044211016906	25 ST




Fuse-disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1107.2</u>	SIK 10/2 LED's(RD)/24V DC BG	4044211016920	25 ST



Fuse-disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige


Article number	Article name	GTIN (EAN)	Packaging unit
<u>1106.2</u>	SIK 10/LED(RD)/115V DC/230V AC BG	4044211016913	25



Fused terminal with disconnect plug, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17042.2</u>	SIK 10/ST BG	4044211155797	25

##INVERSE##CONTA-CONNECT




Fuse-disconnect terminal, Screw connection, Mounting type:Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1101.2</u>	SIK 10 BG	4044211016388	50



Fused terminal, Screw connection, Mounting type:Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17364.4</u>	SIK 10 PA-G BK	4044211178406	50 ST



Fused terminal with disconnect plug, Screw connection, Mounting type:Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17044.2</u>	SIK 10/ST/5x20 BG	4044211155827	25 ST