

Data sheet

2488.1 K 4 GNYE



Cap, Colour: Green-yellow

Business data

Article number	2488.1
Article name	K 4 GNYE
GTIN (EAN)	4044211052836
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	0.8 g
Weight per piece (including packaging)	0.81 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2488.1
Product description	Cap

Data sheet

2488.1 K 4 GNYE



Technical data

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Mounting type	Plug in
---------------	---------

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

Terminal blocks



Clamping yoke, Screw connection, Mounting type: Can be screwed on, Rated cross-section: 4 mm², Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2483.1</u>	ZB 4/K GNYE	4044211052737	50

##INVERSE##CONTA-CONNECT



Clamping yoke, Screw connection, Mounting type: Can be screwed on, Rated cross-section: 4 mm², Colour: natural

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2138.0</u>	ZB 4	4044211049591	50 ST



Clamping yoke, Screw connection, Mounting type: Can be screwed on, Rated cross-section: 4 mm², Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2483.1</u>	ZB 4/K GNYE	4044211052737	50