

Data sheet

17123.8 ADH 185/300 YE



Cover profile, Length: 139.5 mm, Width: 52.9 mm, Colour: Yellow

RAL: 1026

Business data

Article number	<u>17123.8</u>
Article name	ADH 185/300 YE
GTIN (EAN)	4044211177478
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	29 g
Weight per piece (including packaging)	38.5 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	17123.8
Product description	Cover profile

Technical data

Dimensions

Length	139.5 mm
Width	52.9 mm
Height	54 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media


Accessories

##INVERSE##CONTA-CONNECT



High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 185 mm², Width: 55 mm, Colour: Beige


Article number	Article name	GTIN (EAN)	Packaging unit
<u>17024.2</u>	HSKG 185/M12/B/B BG	4044211177423	5 ST



High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 300 mm², Width: 55 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17027.2</u>	HSKG 300/M16/B/B BG	4044211177447	5 ST

##INVERSE##CONTA-CONNECT



High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 300 mm², Width: 55 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17027.2</u>	HSKG 300/M16/B/B BG	4044211177447	5 ST